



Chain lever hoist BRAVO™ with round steel link chain, Safe working load: 0,25t



Order data

Order number	086014 0,25
GTIN	2050001741967
Item class	08Y

Description

Version:

Hoist with **sheet steel casing**, extremely low weight, with **chain release as standard**, **low height**, **rotatable** bearing, forged hook. Exceptionally compact hoist (installed length 240 mm).

Application:

Versatile hoist for use even under the most difficult conditions.

Note:

The principle of the **threaded load pressure brake** is that the axial braking force is generated by the load itself and is thus proportional to the weight of the load. The load is safely held in all positions; to lower it, the difference between the braking torque and load torque must be overcome. All Yale all-purpose hoists are equipped with this device.

The automatic **chain release** permits **quick run-out** of the unloaded chain; when the load is applied, the **threaded load pressure brake** automatically takes effect again and the load is safely held.

The **slip clutch** (optional feature) prevents unduly high loading, and thus increases the working life of the lifting gear.

Hoists with overload protection (slip clutch) available on request.

Technical description

Data sheet

Number of chains	1
Standard lifting height	1.5 m
Lifting force at nominal load	275 daN
Chain link Ø	4 mm
minimum length between hooks	230 mm
Chain link length	12 mm
Safe working load	250 kg
Housing material	Steel
Chain release.	yes
Safe working load in t	0.25 t
Weight	2.2 kg
Type of product	Lever hoist / chain pull