

Garant

**FeedKing high feed rate indexable face mill, with bore, $\varnothing D$ / number of teeth
Z: 100/8mm**


Order data

Order number	212910 100/8
GTIN	4045197411778
Item class	210

Description
Version:

Dynamic cutting edge geometry for highest feed rates. Extremely smooth cutting due to **self-stabilising insert bedding**. **Optimised geometry** for reduced cutting forces, thereby reducing the stress on the main spindle.

Advantage:

Particularly cost-effective due to **exceptionally sturdy 4-edge** inserts.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

Technical description

$\varnothing D_3$	84 mm
Cutting edge $\varnothing D_c$	100 mm
Pack of insert screws	219933 (15IP; 3.8 Nm)
maximum cutting depth $a_{p\max}$	1.15 mm

Mounting bore \varnothing	32 mm
Overall length L_{tot}	50 mm
suitable indexable insert	XD.. 09T308
Number of cutting edges Z	8
Through-coolant	yes
Circular interpolation milling $\varnothing D_{min}$	184 mm
Circular interpolation milling $\varnothing D_{max}$	198 mm
Circular interpolation milling a_p	1.15 mm
Ramping length L for α_{max}	83.5 mm
Ramping angle α_{max}	0.21 degrees
Series	FeedKing
Setting angle κ	9 degrees
Fz Helix	0.7
Shank type	with bore
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Spacing of the cutters	unequal spacing
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Accessories

Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Set of insert screws 10 pieces	219933