

Garant
Circular mill (without insert), Steel, Type: 11

Order data

Order number	217400 11
GTIN	4045197216878
Item class	21Q

Description
Version:

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: no

for insert type: 03

smallest hole $\varnothing D$: 10.6 mm

Internal $\varnothing d_1$: 7.4 mm

maximum cutting depth S_{\max} : 1.6 mm

Overhang L_1 : 17.2 mm

Overall length L_{tot} : 57.2 mm

Technical description

Shank type	Weldon
Set of insert screws	219820 (6 IP; 0.6 Nm)
Overhang L_1	17.2 mm
Shank $\varnothing D_s$ h6	10 mm
Internal $\varnothing d_1$	7.4 mm
maximum cutting depth S_{\max}	1.6 mm
Overall length L_{tot}	57.2 mm
smallest hole $\varnothing D$	10.6 mm
for insert type	03

Through-coolant	no
Material of milling tool	Steel
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219820
-------------------------------	--------