


Indexable face mill 75° MSRS, with bore, Ø D / number of teeth Z: 200/10mm

Order data

Order number	224000 200/10
GTIN	4960664533091
Item class	25P

Description
Version:

Cutter head with normal and close-pitch cutter spacing.

Application:

Cutting depths up to 12 mm and high feed rates for highly efficient roughing. The innovative notched indexable inserts reduce the cutting pressure, which in turn significantly reduces the tendency to vibrate. This allows a larger cutting width and a significantly increased rate of metal removal.

Technical description

Overall length L_{tot}	60 mm
maximum cutting depth $a_{p,max}$	12 mm
Insert screw	229703 (T25; 7.5 Nm)
Cartridge	229765
maximum external $\varnothing D_{max}$	207 mm
Cutting edge $\varnothing D_c$	200 mm
suitable indexable insert	SP.. 1806
Screw for cartridge	229704

Mounting bore \varnothing	60 mm
Number of cutting edges Z	10
Shank type	with bore
Setting angle κ	75 degrees
Through-coolant	no
Machining strategy	HPC
Type of product	Face mill

Accessories

Clamping screw	229703
Cartridge	229765
Clamping screw	229704