

Garant
Indexable drill combination shank Shank Ø 20 mm, 3xD, Ø DC m7: 19,5mm


Order data

Order number	232302 19,5
GTIN	4045197351784
Item class	21S

Description

Version:

High stability and very high process reliability.

With **shank Ø 20 mm**, particularly suitable for **driven tools** (see Group 31).

Application:

For stationary and rotating application.

For holes free of withdrawal scoring and exact dimensional accuracy (approx. ± 0.1 mm).

Also suitable for machines with low drive power. Especially for **MTC (Multi Task Cutting)** use on the new generation of turning/milling centres (**MTM**).

With indexable inserts No. 232400 – 232780.

Suitable for:

Inserts WOEX 030204.

Note:

Counterboring tools with up to 2 steps to your specification available on request. (Minimum order quantity: 2 pieces).

The enquiry form can be found in the eShop on the product page under "Forms".

CAUTION!

A disc falls off when the drill exits.

Risk of injury if the component is rotating.

Please take safety precautions.

Technical description

Number of cutting edges Z	1
Reach L ₁	60 mm
ISO code indexable insert	WOEX 030204

Shank $\varnothing D_s$	20 mm
Pack of insert screws	239700 6IP (0.6 Nm)
Shank length L_s	50 mm
Nominal $\varnothing D$	19.5
Overall length L	134 mm
Maximum adjustment limit V_{max}	0.25 mm
Overhang L_A	84 mm
Drill depth for indexable insert drill up to	3xD
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	oblique spot drilling
Use for drilling	limited cross-drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Machining strategy	MTC
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set 10 pieces Drive 6IP	239700 6IP
Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 6IP	674252 6IP