



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 16/2Lmm



Order data

Order number	225200 16/2L
GTIN	4960664648054
Item class	250

Description

Version:

Cost-efficient due to 4 cutting edges. Without internal cooling.

Technical description

Indexable insert size	10
Insert screw	229713 (8IP; 1.2 Nm)
maximum cutting depth $a_{p\max}$	10 mm
Shank Ø D_s h6	12 mm
Cutting edge Ø D_c	16 mm
Overhang L_1	23 mm
Overall length L_{tot}	100 mm
suitable indexable insert	LOMU..
Number of cutting edges Z	2
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

Accessories

Clamping screw

229713