

**Indexable milling cutter 90° MEC11T, with bore, Ø D / number of teeth Z:  
63/6mm****Order data**

Order number	227310 63/6
GTIN	4960664437504
Item class	250

**Description****Description:**

MEC11T mill type with higher stability due to lower number of cutters than MECX. This enables higher feed rates per cutter.

**Technical description**

Overall length $L_{tot}$	40 mm
Cutting edge Ø $D_c$	63 mm
suitable indexable insert	BD.. 11T3
maximum cutting depth $a_{p\ max}$	10 mm
Mounting bore Ø	22 mm
Insert screw	229708 (T8; 1.2 Nm)
Number of cutting edges Z	6
Ramping angle $\alpha_{max}$	0.2 degrees

Ramping length L for $\alpha_{\max}$	56 mm
Circular interpolation milling $\varnothing D_{\min}$	120 mm
Circular interpolation milling $\varnothing D_{\max}$	124 mm
$\varnothing D_3$	57 mm
Shank type	with bore
Setting angle $\kappa$	90 degrees
Milling application	End milling
Milling application	Circular milling
Milling application	Ramping
Through-coolant	yes
Type of product	End / face mill

---

## Accessories

Clamping screw	229708
----------------	--------