




## Indexable milling cutter 90° MFWN, Plain shank, Ø D / number of teeth Z: 63/4mm



### Order data

Order number	225600 63/4
GTIN	4960664647408
Item class	250

### Description

#### Version:

Milling cutter with double-sided indexable inserts.

The combination of approach angle, chip chamber design as well as the geometries and cutting angles of the indexable inserts ensure outstanding metal removal rates, chip clearance, working life, and low cutting forces, and hence high cost-effectiveness.

### Technical description

Overall length $L_{tot}$	110 mm
maximum cutting depth $a_{p,max}$	8 mm
Cutting edge $\varnothing D_c$	63 mm
Insert screw	229700 (T15; 4.2 Nm)
suitable indexable insert	WNMU 0806..
Shank $\varnothing D_s$ h6	32 mm
Overhang $L_1$	30 mm
Number of cutting edges Z	4
Shank type	Plain shank

Setting angle $\kappa$	90 degrees
Milling application	Plunging
Milling application	End milling
Through-coolant	yes
Type of product	End / face mill

---

## Accessories

Clamping screw	229700
----------------	--------