



Indexable milling cutter 90° MFWN, Plain shank, Ø D / number of teeth Z: 80/5mm



Order data

Order number	225600 80/5
GTIN	4960664647415
Item class	250

Description

Version:

Milling cutter with double-sided indexable inserts.

The combination of approach angle, chip chamber design as well as the geometries and cutting angles of the indexable inserts ensure outstanding metal removal rates, chip clearance, working life, and low cutting forces, and hence high cost-effectiveness.

Technical description

Cutting edge Ø D _c	80 mm
Overall length L _{tot}	110 mm
Shank Ø D _s h6	32 mm
maximum cutting depth a _{p,max}	8 mm
Insert screw	229700 (T15; 4.2 Nm)
suitable indexable insert	WNMU 0806..
Overhang L ₁	30 mm
Number of cutting edges Z	5
Shank type	Plain shank

Setting angle κ	90 degrees
Milling application	Plunging
Milling application	End milling
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229700
----------------	--------