

Garant

**TwinCut indexable face mill 45° wide pitch, with bore, Ø D / number of teeth
Z: 50/3mm**

**Order data**

Order number	213410 50/3
GTIN	4045197605429
Item class	210

Description**Version:**

From Ø 160 mm for arbors to DIN 2079, with 4 additional attachment holes and without internal cooling.

Application:

With double-sided 8-edge inserts (ON.U) or 4-edge inserts (SN.U).

Spare part:

Shim No. 219897 for use with both types of indexable insert.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.
Do not mix different types of insert ON.U and SN.U.

Technical description

Shim	219897
Pack of insert screws	219898 (15IP; 3.8 Nm)
suitable indexable insert	SN.U

suitable indexable insert	ON.U
maximum external $\varnothing D_{\max}$ for SN.U inserts	65.2 mm
maximum external $\varnothing D_{\max}$ for ON.U inserts	61.8 mm
Cutting edge $\varnothing D_c$	50 mm
Overall length L_{tot} for ON.U inserts	38.3 mm
Mounting bore \varnothing	22 mm
Overall length L_{tot} for SN.U inserts	40 mm
Clamp screw for shim	219899
Number of cutting edges Z	3
Series	TwinCut
Shank type	with bore
Setting angle κ	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Face mill

Accessories

Pack of insert screws 10 pieces	219898
Clamping screw	219899
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Shim	219897