



Shoulder mill 90° MEW with plain shank, for indexable inserts LO..



Order data

Order number	225200 20/2
GTIN	4960664648092
Item class	250

Description

Version:

Cost-efficient due to 4 cutting edges.

Technical description

Shank $\varnothing D_s$ h6	20 mm
maximum cutting depth $a_{p \max}$	10 mm
Indexable insert size	10
Overall length L_{tot}	110 mm
suitable indexable insert	LOMU..
Overhang L_1	30 mm
Insert screw	229713 (8IP; 1.2 Nm)
Cutting edge $\varnothing D_c$	20 mm
Number of cutting edges Z	2
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/225200-20/2>
