



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 40/3Lmm



Order data

Order number	225200 40/3L
GTIN	4960664648290
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

Cutting edge Ø D _c	40 mm
suitable indexable insert	LOMU..
Insert screw	229714 (15IP; 3.5 Nm)
Shank Ø D _s h6	32 mm
Overall length L _{tot}	150 mm
Overhang L ₁	50 mm
Indexable insert size	15
maximum cutting depth a _{p,max}	15 mm
Number of cutting edges Z	3
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

Accessories

Clamping screw

229714