



Indexable milling cutter 90° MFWN, with bore, Ø D / number of teeth Z: 125/8mm



Order data

Order number	225615 125/8
GTIN	4960664647705
Item class	250

Description

Version:

Milling cutter with double-sided indexable inserts.

The combination of approach angle, chip chamber design as well as the geometries and cutting angles of the indexable inserts ensure outstanding metal removal rates, chip clearance, working life, and low cutting forces, and hence high cost-effectiveness.

Technical description

suitable indexable insert	WNMU 0806..
Overall length L_{tot}	63 mm
maximum cutting depth $a_{p,max}$	8 mm
Mounting bore Ø	40 mm
Cutting edge Ø D_c	125 mm
Insert screw	229700 (T15; 4.2 Nm)
Number of cutting edges Z	8

Shank type	with bore
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229700
----------------	--------