

Garant

TwinCut indexable face mill 45° normal pitch, with bore, Ø D / number of teeth Z: 100/7mm

**Order data**

Order number	213415 100/7
GTIN	4045197605511
Item class	210

Description**Version:**

From Ø 160 mm for arbors to DIN 2079, with 4 additional attachment holes and without internal cooling.

Application:

With double-sided 8-edge inserts (ON.U) or 4-edge inserts (SN.U).

Spare part:

Shim No. 219897 for use with both types of indexable insert.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.
Do not mix different types of insert ON.U and SN.U.

Technical description

Overall length L_{tot} for SN.U inserts	50 mm
maximum external $\varnothing D_{\text{max}}$ for ON.U inserts	111.8 mm
Cutting edge $\varnothing D_c$	100 mm

Clamp screw for shim	219899
suitable indexable insert	SN.U
suitable indexable insert	ON.U
Shim	219897
Overall length L_{tot} for ON.U inserts	48.3 mm
Pack of insert screws	219898 (15IP; 3.8 Nm)
maximum external $\varnothing D_{max}$ for SN.U inserts	115.2 mm
Mounting bore \varnothing	32 mm
Number of cutting edges Z	7
Series	TwinCut
Shank type	with bore
Setting angle κ	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Pack of insert screws 10 pieces	219898
Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Shim	219897
Clamping screw	219899