




Solid carbide milling cutter, uncoated, \varnothing e8 DC: 5mm



Order data

Order number	202238 5
GTIN	4067263238201
Item class	12X

Description

Version:

Eccentric relief ground, additionally **finish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Application:

For roughing and finishing.

Technical description

Shank $\varnothing D_s$	6 mm
Corner chamfer angle	90 degrees
Corner chamfer width at 45°	0.1 mm
Feed f_z for slot milling in short-chipping aluminium	0.015 mm
Helix angle	45 degrees
Tolerance nominal \varnothing	e8
Feed f_z for side milling in short-chipping aluminium	0.02 mm
Cutting edge $\varnothing D_c$	5 mm
Shank	DIN 6535 HA to h6
Overall length L	65 mm
Flute length L_c	15 mm
Direction of infeed	horizontal, oblique and vertical
No. of teeth Z	3

Coating	uncoated
Tool material	Solid carbide
Standard	Works standard
Type	W
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	105 m/min	N
PMMA acrylic	suitable	160 m/min	N
PE-HD	suitable	110 m/min	N
PA 66	suitable	130 m/min	N
PEEK	suitable	110 m/min	N
PF 31	suitable	90 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	160 m/min	N
Cu	suitable	120 m/min	N
CuZn	suitable	150 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air

suitable only under
restricted conditions

Services

Shank grinding Type HB

129100 HB