

**metabo****Cordless hammer drill with Li-ion battery, Type: SB18LTBL****Order data**

Order number	070121 SB18LTBL
GTIN	4007430334718
Item class	03D

**Description****Version:****Cordless hammer drill with brushless motor and two-speed gearbox.**

Choose between a complete set of 2 battery packs, charger and sturdy plastic case or the machine without accessories in a box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

By the way, all Metabo battery packs come with a 3-year warranty, irrespective of the number of charging cycles.

Further details such as the bright LED work light and the handy belt hook ensure even more comfort when working. All LT and LTX models are equipped with a high-performance impact mechanism for maximum drilling performance in stone and masonry. The pulse operation of the LTX class provides effective help when screws are tight or when spot drilling on smooth surfaces. For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

- **Cordless hammer drill with optimum performance for demanding applications.**
- **High-performance striking mechanism for best work results.**
- **Integrated work light for illuminating the working area.**
- **With practical belt hook and bit depot, optionally fixable on the right or left.**
- **LiHD battery pack for ultimate performance, ultra-long life and durability.**

- **Many brands, one battery system: this product can be combined with all 18V battery packs and chargers of the CAS brands.**

**Advantage:**

**Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

**Supplied with:**

Includes quick-clamping drill chuck, 2x LiHD rechargeable batteries, charger and metaBox.

**Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

## Technical description

Battery voltage	18 V
No load speed	0 - 600
No load speed	0 - 2100
Number of rechargeable batteries contained	2
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in concrete	13 mm
maximum torque hard	75 Nm
maximum twist drill size Ø in wood	38 mm
maximum twist drill size Ø in steel	13 mm
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Motor design	brushless
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Manufacturer's designation	SB 18 LT BL
maximum torque soft	34 Nm
Battery capacity	4 Ah
Weight without battery	1.2 kg
Packaging	Metabox
Weight including rechargeable battery	1.8 kg
typical application	Strong

maximum hammer rate	31950 min <sup>-1</sup>
Type of product	Impact drill /screwdriver