

metabo**Cordless impact wrench including LiHD rechargeable battery, Type: 18LTX800**

Order data

Order number	074060 18LTX800
GTIN	4061792228719
Item class	03D

Description

Version:

High torques for heavy-duty screwdriving applications.

The LTX-class cordless impact wrenches are available with a maximum torque of 300 Nm, 800 Nm or 1750 Nm. Perfectly suited for power-intensive screwdriving in all performance ranges. They are also equipped with an Automatic Power Shift (APS) mode:

- **Unscrewing in APS mode: prevents the screw/nut from falling through automatic reduction of speed after loosening.**
- **Bolting in APS mode: prevents the screw/nut from overturning through automatic switching off after the first impact.**

By the way, all Metabo battery packs come with a 3-year warranty, irrespective of the number of charging cycles.

Further details such as the bright LED work light ensure even more comfort when working.

- **Powerful cordless impact wrench with 1/2 inch external square drive and 800 Nm.**
- **Unique Metabo brushless motor for quick working and maximum efficiency with every use.**
- **High torque combined with a particularly handy design.**
- **Very powerful for heavy screwdriving applications.**
- **Low-recoil operation with very high torque.**
- **Twelve speed/torque levels for a wide range of applications.**
- **Integral work light for illuminating the working area.**

- **Sturdy die-cast aluminium gearbox casing for optimum heat dissipation and a long service life.**
- **With handy belt hook, can be fixed either on the left or right.**
- **LiHD battery pack for ultimate performance, extremely long operating life and service life.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

Supplied with:

Supplied with 2× LiHD rechargeable batteries, charger and metaBOX.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Type of rechargeable battery	Lithium-ion
maximum torque	800 Nm
Weight without battery	1.95 kg
Tool arbor size	1/2 in
maximum break-away torque	1200 Nm
Torque settings	12
Power supply	Mains operated
Toolholder	External square drive
Battery voltage	18 V
typical application	Heavy Duty
Packaging	Metabox
Motor design	brushless
Battery capacity	5.5 Ah
Number of rechargeable batteries contained	2
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Manufacturer's designation	SSW 18 LTX 800 BL
maximum hammer rate	3300 min ⁻¹
Weight including rechargeable battery	2.9 kg

No load speed	0 - 2575 min ⁻¹
Type of product	Impact wrench