

Garant
Circular mill, Carbide, Type: 27L

Order data

Order number	217252 27L
GTIN	4045197216557
Item class	21Q

Description
Note:

The actual groove depth S_{max} is calculated as follows: $(D-d_1) / 2$.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: P26

smallest hole $\varnothing D$: 22 - 37 mm

Internal $\varnothing d_1$: 15.5 mm

maximum cutting depth S_{max} : 10.75 mm

Overhang L_1 : 25 mm

Overall length L_{tot} : 109.6 mm

Technical description

Overall length L_{tot}	109.6 mm
Shank $\varnothing D_s$ h6	16 mm
Set of insert screws	219819 (20IP; 5.7 Nm)
Internal $\varnothing d_1$	15.5 mm
Shank type	cylindrical
smallest hole $\varnothing D$	22 - 37 mm
maximum cutting depth S_{max}	10.75 mm
Overhang L_1	25 mm

Shank	DIN 6535 HA
for insert type	P26
Through-coolant	yes
Thread depth	21.5 mm
Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219819
-------------------------------	--------