

Garant**GARANT Master Mute cutting head, right-hand, System / insert size: DM/8****Order data**

Order number	264838 DM/8
GTIN	4067263707912
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SVUCR

suitable indexable insert: VC.. 1604..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre offset L_3 : 27 mm

Technical description

Centre offset L_3	27 mm
Overall length L	32 mm

ISO code cutting head	SVUCR
Series	Master Mute
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Approach angle	93 °
Insert screw	269028 49
Cutting point / joint	40 mm
System	DM
suitable indexable insert	VC.. 1604..
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head