

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: DM/5**

**Order data**

Order number	264838 DM/5
GTIN	4067263707882
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SCLCR

suitable indexable insert: CC.. 1204..

Approach angle: 95 °

Minimum pre-drill  $\varnothing D_{\min}$ : 50 mm

Centre offset  $L_3$ : 27 mm

**Technical description**

System	DM
Minimum pre-drill $\varnothing D_{\min}$	50 mm

Insert screw	269028 49
Cutting point / joint	40 mm
Overall length L	27 mm
ISO code cutting head	SCLCR
Approach angle	95 °
Centre offset L <sub>3</sub>	27 mm
suitable indexable insert	CC.. 1204..
Series	Master Mute
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head