



Indexable milling cutter 90° MEC11T, Plain shank, Ø D / number of teeth Z: 22/3Lmm



Order data

Order number	227300 22/3L
GTIN	4960664396085
Item class	250

Description

Description:

MEC11T mill type with higher stability due to lower number of cutters than MECX. This enables higher feed rates per cutter.

Technical description

Shank Ø D _s h6	20 mm
Overall length L _{tot}	110 mm
Cutting edge Ø D _c	22 mm
maximum cutting depth a _{p max}	10 mm
Overhang L ₁	26 mm
Insert screw	229708 (T8; 1.2 Nm)
suitable indexable insert	BD.. 11T3
Number of cutting edges Z	3
Ramping length L for α _{max}	15 mm
Circular interpolation milling Ø D _{max}	42 mm
Circular interpolation milling Ø D _{min}	38 mm
Ramping angle α _{max}	0.76 degrees
Ø D ₃	16 mm

Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Ramping
Milling application	Circular milling
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229708
----------------	--------