

**Garant**
**GARANT Master Mute cutting head, left-hand, System / insert size: DM/6**

**Order data**

Order number	264839 DM/6
GTIN	4067263707998
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SDUCL

suitable indexable insert: DC.. 11T3..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 50 mm

Centre offset  $L_3$ : 27 mm

**Technical description**

System	DM
Overall length L	32 mm

Insert screw	269028 50
Cutting point / joint	40 mm
Centre offset L <sub>3</sub>	27 mm
suitable indexable insert	DC.. 11T3..
Series	Master Mute
Minimum pre-drill $\varnothing D_{\min}$	50 mm
ISO code cutting head	SDUCL
Approach angle	93 °
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head