

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: DM/2

Order data

Order number	264839 DM/2
GTIN	4067263707950
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: PDUNL

suitable indexable insert: DN.. 1506..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

ISO code cutting head	PDUNL
Centre offset L_3	27 mm

Minimum pre-drill $\varnothing D_{\min}$	50 mm
Overall length L	26 mm
Lever screw	259018 18
suitable indexable insert	DN.. 1506..
System	DM
Approach angle	93 °
Shim	269005 14
Series	Master Mute
Cutting point / joint	40 mm
Lever	259015 19
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head