

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: DM/1

Order data

| | |
|--------------|---------------|
| Order number | 264839 DM/1 |
| GTIN | 4067263707943 |
| Item class | 29D |

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: PCLNL

suitable indexable insert: CN.. 1204..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

| | |
|------------------------------------------|-------|
| Overall length L | 26 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 50 mm |

| | |
|------------------------------|--------------|
| Centre offset L ₃ | 27 mm |
| Lever screw | 259018 18 |
| suitable indexable insert | CN.. 1204.. |
| Approach angle | 95 ° |
| Shim | 269005 13 |
| Series | Master Mute |
| System | DM |
| Lever | 259015 18 |
| ISO code cutting head | PCLNL |
| Cutting point / joint | 40 mm |
| Application type | left-hand |
| Through-coolant | yes |
| Type of product | Cutting head |