

**Garant**
**Circular mill (without insert), Carbide, Type: 11L**

**Order data**

Order number	217405 11L
GTIN	4045197216915
Item class	21Q

**Description**
**Version:**

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: no

for insert type: 03

smallest hole  $\varnothing D$ : 10.6 mm

Internal  $\varnothing d_1$ : 7.4 mm

maximum cutting depth  $S_{\max}$ : 1.6 mm

Overhang  $L_1$ : 34.2 mm

Overall length  $L_{\text{tot}}$ : 74.2 mm

**Technical description**

Set of insert screws	219820 (6 IP; 0.6 Nm)
Internal $\varnothing d_1$	7.4 mm
Shank type	Weldon
Shank $\varnothing D_s$ h6	10 mm
Overhang $L_1$	34.2 mm
maximum cutting depth $S_{\max}$	1.6 mm
smallest hole $\varnothing D$	10.6 mm
Overall length $L_{\text{tot}}$	74.2 mm
for insert type	03

Through-coolant	no
Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

---

## Accessories

Set of insert screws 10-piece	219820
-------------------------------	--------