

metabo**Cordless drill / driver without rechargeable battery with Quick System, Type: BSLTX3BLQI****Order data**

Order number	070271 BSLTX3BLQI
GTIN	4061792211643
Item class	03D

Description**Version:****Cordless drill drivers with and without Metabo Quick System.**

The **Quick System saves a lot of time** when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

- **Selectable pulse operation for unscrewing fixed screws and spot drilling on smooth surfaces.**
- **Precision stop: electronic torque coupling with increased precision for precise and sensitive working.**
- **Extremely powerful 3-speed drill/driver with high speed for extended use and even faster drilling progress, especially in heavy metal applications.**
- **Powerful drill chuck with post-tensioning function to prevent slippage of the insert tool and maximum concentricity.**

- **Metabo QuickPlus system: quickly change the toolholder and insertion tool for flexible working with maximum loads.**
- **Overload protection to protect the motor against overheating.**
- **Electronic safety shut-off function: no kick-back when the drill is blocked, providing excellent protection for the operator.**
- **With handy belt hook and bit holder, can be fixed either on the left or right.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

With quick-change drill chuck, without battery, without charger.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Motor design	brushless
maximum torque soft	65 Nm
Quick-clamping chuck range	1.5 - 13 mm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
typical application	Heavy Duty
Power supply	Mains operated
maximum twist drill size Ø in steel	16 mm
maximum twist drill size Ø in wood	68 mm
Number of rechargeable batteries contained	0
Packaging	Metabox
maximum torque hard	130 Nm
Manufacturer's designation	BS 18 LTX-3 BL Q I
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
No load speed	0 - 450 min ⁻¹
No load speed	0 - 2000 min ⁻¹

No load speed	0 - 4000 min ⁻¹
Weight including rechargeable battery	3 kg
Weight without battery	2 kg
Type of product	Drill/drivers
USP1	18V
USP2	Brushless motor, quick-change chuck clamping range 1.5-13, without battery

Accessories

Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery charger Type ASC55	073890 ASC55