

metabo
Drill, Type: BE650**Order data**

Order number	075070 BE650
GTIN	4061792201644
Item class	03D

Description**Version:****The right drill for every hole diameter.**

Each drill has an optimum speed range for specific drilling diameters, as well as a spindle with hexagon socket for screwdriver bits for use even without a drill chuck. The Futuro Plus quick-clamping drill chuck ensures exact drilling results by means of automatic retightening during drilling.

- **Small, handy drilling machine.**
- **Vario (V) electronics ensure you work at speeds that are suitable for the material.**
- **Adjustment wheel for pre-selecting the speed**
- **Reversible.**
- **Handle with non-slip softgrip surface.**

Supplied with:

Includes Futuro Plus quick-clamping drill chuck.

Technical description

Reversible	yes
Maximum twist drill size Ø in steel 1st speed	13 mm

Power consumption	650 W
Clamping neck Ø	43 mm
Chuck clamping range	1.5 - 13 mm
maximum twist drill size Ø in wood 1st speed	30 mm
maximum speed 1st speed	1500 min ⁻¹
Manufacturer's designation	BE 650
Weight	1.8 kg
Cable length	2.5 m
Power supply	Mains-powered
Type of product	Drill