

metabo**Impact drill, Type: SBE780-2****Order data**

Order number	075710 SBE780-2
GTIN	4007430313454
Item class	03D

Description**Version:****Impact drilling with high user protection.**

The impact drills are equipped with the Metabo S-automatic safety clutch. When the drill is blocked, the drive is immediately mechanically decoupled to minimise the reverse torque to the user.

- **Metabo Marathon motor with dust protection for long life.**
- **Spindle with hexagon socket for screwdriver bits enables use without a drill chuck.**
- **Vario (V) electronics for working at material-appropriate speeds.**
- **Adjusting wheel for preselecting the speed.**
- **Robust die-cast aluminum gear housing for optimum heat dissipation and durability.**
- **Rotating carbon brush bridge for maximum performance even in anti-clockwise rotation, e.g. for unscrewing stuck screws.**
- **Anti-clockwise.**
- **Cable-friendly ball grommet for optimum freedom of movement when working.**

Technical description

maximum twist drill size Ø in concrete	18 mm
Manufacturer's designation	SBE 780-2
Cable length	4 m
Packaging	Metabox

Power consumption	780 W
maximum twist drill size Ø in wood	25 mm
maximum twist drill size Ø in wood	40 mm
maximum speed 1st speed	680 min ⁻¹
maximum twist drill size Ø in steel	8 mm
maximum twist drill size Ø in steel	13 mm
maximum torque	13 Nm
maximum torque	32 Nm
Power supply	Mains-powered
Weight	2.6 kg
maximum speed 2nd speed	1900 min ⁻¹
maximum hammer rate	58900 min ⁻¹
Chuck clamping range	1.5 - 13 mm
No load speed	0 - 1100 min ⁻¹
No load speed	0 min ⁻¹
Type of product	Impact drill