

metabo**Impact drill, Type: SBEV1300-2****Order data**

Order number	075710 SBEV1300-2
GTIN	4007430312723
Item class	03D

Description**Version:****Impact drilling with high user protection.**

The impact drills are equipped with the Metabo S-automatic safety clutch. When the drill is blocked, the drive is immediately mechanically decoupled to minimise the reverse torque to the user.

- **Restart protection: Prevents unintentional start-up after power interruption.**
- **Selectable pulse mode for unscrewing jammed screws and spot drilling on smooth surfaces.**
- **Adjusting wheel for preselecting the speed.**
- **Metabo Marathon motor with dust protection for long life.**
- **Spindle with hexagon socket for screwdriver bits enables use without a drill chuck.**
- **Vario-Tacho-Constamatic (VTC): full-wave electronics for working with material-appropriate speeds that remain constant under load.**
- **Adjusting wheel for preselecting the speed.**
- **Robust die-cast aluminum gear housing for optimum heat dissipation and durability.**
- **Rotating carbon brush bridge for maximum performance even in anti-clockwise rotation, e.g. for unscrewing stuck screws.**
- **Anti-clockwise.**
- **Overload protection: protects the motor from overheating.**
- **Cable-friendly ball grommet for optimum freedom of movement when working.**
- **Carbon brush wear indicator.**

Supplied with:

Includes quick-clamping chuck, additional handle, depth stop and metaBOX.

Technical description

maximum twist drill size Ø in concrete	22 mm
Weight	2.8 kg
Cable length	4 m
maximum hammer rate	58900 min ⁻¹
maximum twist drill size Ø in steel	10 mm
maximum twist drill size Ø in steel	16 mm
maximum torque	16 Nm
maximum torque	44 Nm
maximum speed 2nd speed	3100 min ⁻¹
Packaging	Metabox
Manufacturer's designation	SBEV 1300-2
Power consumption	1300 W
maximum speed 1st speed	1100 min ⁻¹
maximum twist drill size Ø in wood	25 mm
maximum twist drill size Ø in wood	40 mm
Power supply	Mains-powered
Chuck clamping range	1 - 13 mm
No load speed	0 - 1100 min ⁻¹
No load speed	0 - 3100 min ⁻¹
Type of product	Impact drill