

metabo**Orbital sander, Type: SR2185****Order data**

Order number	077332 SR2185
GTIN	4007430270986
Item class	03D

Description**Version:****Lightweight, handy 210 W orbital sander with perfect ergonomics:**

- **Handle area with non-slip softgrip surface.**
- **Excellent surface finish without grinding rings and grooves for professional surface treatment.**
- **Suction option by connecting an all-purpose vacuum cleaner.**

Supplied with:

Supplied with dust bag, carrying case.

Note:

For suitable hook and loop sanding paper see No. 557576.

Technical description

Hole pattern	8-fold
Weight	1.5 kg
Abrasive paper length (hook and loop)	184 mm
Orbital stroke	2 mm
Manufacturer's designation	SR 2185
maximum vibration to EN	< 4 m/s ²
Abrasive paper length (clamped)	230 mm

Speed of oscillation	22300 min ⁻¹
Power supply	Mains-powered
Abrasive paper width (hook and loop)	92 mm
Abrasive paper width (clamped)	92 mm
Power consumption	210 W
Packaging	Carrying case
Type of product	Orbital sanders