

Garant
Circular mill (without insert), Carbide, Type: 11XL

Order data

Order number	217405 11XL
GTIN	4045197216922
Item class	21Q

Description
Version:

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: 03

smallest hole $\varnothing D$: 10.6 mm

Internal $\varnothing d_1$: 8 mm

maximum cutting depth S_{\max} : 1.25 mm

Overall length L_{tot} : 77.66 mm

Shank $\varnothing D_s$ h6: 8 mm

Technical description

Shank type	cylindrical
Shank $\varnothing D_s$ h6	8 mm
Internal $\varnothing d_1$	8 mm
smallest hole $\varnothing D$	10.6 mm
Overall length L_{tot}	77.66 mm
Set of insert screws	219820 (6 IP; 0.6 Nm)
maximum cutting depth S_{\max}	1.25 mm
for insert type	03
Through-coolant	yes

Thread depth	40 mm
Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219820
-------------------------------	--------