

metabo
Straight die grinder, Type: GE710C

Order data

| | |
|--------------|---------------|
| Order number | 077264 GE710C |
| GTIN | 4007430212313 |
| Item class | 03D |

Description
Version:

The straight die grinders from Metabo® are among the slimmest and most compact machines on the market. The powerful motors of the mains-operated and cordless straight die grinders offer maximum productivity with high precision in all applications.

- **Precise collar for stationary use.**
- **Pre-selectable speed levels.**
- **Electronic safety shutdown of the motor when the tool is blocked to ensure safe working.**

Particularly short, **compact design** for working on inner curves or other narrow points.

Supplied with:

Collet 6 mm, 2 open-ended spanners.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

| | |
|--------------------------------|---------------------------------|
| Weight | 1.4 kg |
| Speed range | 13000 - 34000 min ⁻¹ |
| maximum collet Ø | 6 mm |
| Power supply | Mains-powered |
| Power consumption | 710 W |
| electronic speed pre-selection | yes |
| Manufacturer's designation | GE 710 Compact |

| | |
|-------------------------|----------------------|
| maximum vibration to EN | 6.8 m/s ² |
| Type of product | Straight die grinder |