

metabo
Straight die grinder, Type: GE950GP

Order data

Order number	077264 GE950GP
GTIN	4007430212412
Item class	03D

Description
Version:

The straight die grinders from Metabo® are among the slimmest and most compact machines on the market. The powerful motors of the mains-operated and cordless straight die grinders offer maximum productivity with high precision in all applications.

- **Precise collar for stationary use.**
- **Pre-selectable speed levels.**
- **Electronic safety shutdown of the motor when the tool is blocked to ensure safe working.**

The straight grinders with a **long grinding spindle** are **ideal for deburring** or grinding weld seams in hard-to-reach places.

With **reduced speed range** for powerful grinding with flap grinding wheels.

Supplied with:

Collet 6 mm, rubber protection cap, additional handle, 1 open-ended spanner.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Weight	1.7 kg
electronic speed pre-selection	yes
Manufacturer's designation	GE 950 G
maximum vibration to EN	< 2.5 m/s ²

Power consumption	950 W
maximum collet Ø	6 mm
Power supply	Mains-powered
Speed range	2500 - 8700 min ⁻¹
Type of product	Straight die grinder