

**Garant**
**Circular mill (without insert), Carbide, Type: 20L**

**Order data**

Order number	217405 20L
GTIN	4045197216939
Item class	21Q

**Description**
**Version:**

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: 02

smallest hole  $\varnothing D$ : 17.5 mm

Internal  $\varnothing d_1$ : 12.2 mm

maximum cutting depth  $S_{\max}$ : 2.6 mm

Overhang  $L_1$ : 63.7 mm

Overall length  $L_{\text{tot}}$ : 108.7 mm

**Technical description**

smallest hole $\varnothing D$	17.5 mm
Internal $\varnothing d_1$	12.2 mm
Shank $\varnothing D_s$ h6	12 mm
Shank type	Weldon
Overall length $L_{\text{tot}}$	108.7 mm
Set of insert screws	219821 (15 IP; 3.0 Nm)
maximum cutting depth $S_{\max}$	2.6 mm
Overhang $L_1$	63.7 mm
for insert type	02

Through-coolant	yes
Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

---

## Accessories

Set of insert screws 10-piece	219821
-------------------------------	--------