


DNMG 150604, Grade: CCX

Order data

Order number	250696 CCX
GTIN	4960664900879
Item class	25E

Description

DNMG 150604 CCX Grade: CCX
 Chip breaker: PP
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.05 - 0.35 mm/rev.
 Cutting speed v_c main application: 210 - 450 m/min

Technical description

Chip breaker	PP
Finishing/roughing assignment	Finishing
Main application	P
ISO code indexable insert	DNMG 150608
Corner radius	0.8 mm
Cutting conditions	continuous
Cutting depth a_p	0.2 - 1.5 mm

Cutting speed v_c main application	210 - 450 m/min
Number of changes/inserts	4
Coating	coated
Tool material	Cermet
Feed f	0.05 - 0.35 mm/rev.
Grade	CCX
Type of product	Indexable insert for turning