

**DNMG 150608, Grade: CCX****Order data**

Order number	250697 CCX
GTIN	4960664900886
Item class	25E

**Description**

DNMG 150608 CCX Grade: CCX  
Chip breaker: PP  
Cutting depth  $a_p$ : 0.2 - 1.5 mm  
Feed  $f$ : 0.05 - 0.35 mm/rev.  
Cutting speed  $v_c$  main application: 210 - 450 m/min

**Technical description**

Coating	coated
Number of changes/inserts	4
Corner radius	0.8 mm
Grade	CCX
Main application	P
Finishing/roughing assignment	Finishing
Feed $f$	0.05 - 0.35 mm/rev.

Cutting speed $v_c$ main application	210 - 450 m/min
Tool material	Cermet
Cutting conditions	continuous
ISO code indexable insert	DNMG 150608
Cutting depth $a_p$	0.2 - 1.5 mm
Chip breaker	PP
Type of product	Indexable insert for turning