


VNMG 160404, Grade: CCX

Order data

Order number	251752 CCX
GTIN	4960664900954
Item class	25E

Technical description

Corner radius	0.4 mm
Main application	P
Cutting conditions	continuous
ISO code indexable insert	VNMG 160404
Tool material	Cermet
Number of changes/inserts	4
Cutting speed v_c main application	210 - 450 m/min
Coating	coated
Chip breaker	PP
Cutting depth a_p	0.2 - 1.5 mm
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.3 mm/rev.

Grade	CCX
Type of product	Indexable insert for turning