


**Garant****Milling insert 60°, HB7720, Pitch: 2mm****Order data**

Order number	217279 2
GTIN	4045197543004
Item class	21C

**Description****Note:**

**Corrected profile threading inserts** eliminate the need to program a correction to the diameter. Therefore use these inserts only for the specified thread sizes.

When using the circular mill No. 217252 size 18L and 18XL, the partial profile insert No. 217281 size 1–4 can be used only up to pitch 3.0.

**Technical description**

for threads $\geq$	M16x2
Depth t	1.16 mm
Insert geometry	Full profile
External $\varnothing$ D	10.5 mm
Number of clamping slots	3
Thread pitch	2 mm
Application	Internal
Grade	HB7720

Tool material	Carbide
Thread type	MF
Thread type	M
Thread type	MF-LH
Thread type	M-LH
Flank angle	60 degrees
Type	P12
Number of cutting edges Z	3
Cutting direction	right-hand and left-hand
Type of product	Cutter insert for circular milling

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	500 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	250 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	250 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 55 HRC	suitable	60 m/min	H
Steel < 60 HRC	suitable	45 m/min	H
Steel < 65 HRC	suitable	35 m/min	H
Steel < 67 HRC	suitable	30 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	120 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	120 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	80 m/min	S

GG(G)	suitable	180 m/min	K
Uni	suitable		
wet maximum	suitable		
dry	suitable		