

Garant
Circular mill (without insert), Carbide, Type: 20XL

Order data

Order number	217405 20XL
GTIN	4045197216946
Item class	21Q

Description
Version:

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: 02

smallest hole $\varnothing D$: 17.5 mm

Internal $\varnothing d_1$: 12.2 mm

maximum cutting depth S_{\max} : 2.6 mm

Overall length L_{tot} : 121.5 mm

Shank $\varnothing D_s$ h6: 12 mm

Technical description

Set of insert screws	219821 (15 IP; 3.0 Nm)
smallest hole $\varnothing D$	17.5 mm
Internal $\varnothing d_1$	12.2 mm
Shank $\varnothing D_s$ h6	12 mm
maximum cutting depth S_{\max}	2.6 mm
Shank type	cylindrical
Overall length L_{tot}	121.5 mm
for insert type	02
Through-coolant	yes

Thread depth	62.5 mm
Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219821
-------------------------------	--------