


**DC.T 11T304, Grade: CCX**

**Order data**

Order number	260386 CCX
GTIN	4960664911585
Item class	25E

**Description**
**Technical description**

Number of changes/inserts	2
Main application	P
Corner radius	0.4 mm
Tolerance	M
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.3 mm/rev.
Chip breaker	PP
Cutting speed $v_c$ main application	150 - 370 m/min
Tool material	Cermet
Grade	CCX
Cutting conditions	continuous

Cutting depth $a_p$	0.1 - 1 mm
Coating	coated
ISO code indexable insert	DCMT11T304
Type of product	Indexable insert for turning