


DNMG 150608, Grade: CA315

Order data

Order number	250797 CA315
GTIN	4960664799053
Item class	25E

Technical description

Tool material	Carbide
Main application	O
Number of changes/inserts	4
ISO code indexable insert	DNMG 150608
Corner radius	0.8 mm
Cutting speed v_c main application	150 - 350 m/min
Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
Chip breaker	KG
Coating	coated
Grade	CA315
Feed f	0.17 - 0.5 mm/rev.

Cutting depth a_p	0.5 - 3.6 mm
Type of product	Indexable insert for turning