

**Garant****Indexable thread mill, Weldon shank, Effective  $\varnothing$  DW / Overhang L1:  
37/58mm****Order data**

Order number	218000 37/58
GTIN	4045197411877
Item class	21R

**Description****Application:**

- For parallel internal and external threads; other inserts and taper thread tools available on request.
- For threads in through holes and blind holes.
- For universal use cutting left-hand and right-hand threads.
- No chip clearance problems, since only short chips are produced.
- Low cutting pressure.

**Note:**

Version with double HB drive flat.

**Technical description**

Overhang L <sub>1</sub>	58 mm
Shank $\varnothing$ D <sub>s</sub>	32 mm
Effective $\varnothing$ D	37 mm
Clamping screw	219925
Insert size	27
Number of cutting edges Z	1
Number of clamping slots	1
Overall length L	120 mm

Shank type	Weldon shank
Application for type of drilling	Blind hole
Application for type of drilling	Through hole
Cutting direction	left-hand and right-hand
Through-coolant	yes
Type of product	thread milling cutter

---

## Accessories

Clamping screw	219925
----------------	--------