

**Garant**
**High performance indexable thread mill, Weldon shank, Effective  $\varnothing D$  / Overhang  $L_1$ : 17/26mm**

**Order data**

Order number	218050 17/26
GTIN	4045197411785
Item class	21R

**Description**
**Version:**

**HPC thread milling cutters for reduced machining times.**

**Application:**

For general use on **right-hand and left-hand internal and external threads**. For threads in **through holes** and **blind holes**.

**Note:**

Thread mill No. 218050 sizes 17/26 and 17/36 suitable for pitches up to and including 2.5 mm.  
Thread mill No. 218050 sizes 30/65 suitable for pitches up to < 5.

**Technical description**

Insert size	25
Shank $\varnothing D_s$	25 mm
Overhang $L_1$	26 mm
Effective $\varnothing D$	17 mm
Overall length $L_{tot}$	85 mm
Fixing screw	219926
Number of cutting edges Z	2
Number of clamping slots	2
Shank type	Weldon shank

Application for type of drilling	Blind hole
Application for type of drilling	Through hole
Cutting direction	left-hand and right-hand
Through-coolant	yes
Type of product	thread milling cutter

---

## Accessories

Clamping screw	219926
----------------	--------