

Garant**Indexable thread mill, Weldon shank, Effective Ø DW / Overhang L1:
37/98mm****Order data**

Order number	218000 37/98
GTIN	4045197411884
Item class	21R

Description**Application:**

- For parallel internal and external threads; other inserts and taper thread tools available on request.
- For threads in through holes and blind holes.
- For universal use cutting left-hand and right-hand threads.
- No chip clearance problems, since only short chips are produced.
- Low cutting pressure.

Note:

Version with double HB drive flat.

Technical description

Insert size	27
Shank Ø D _s	32 mm
Clamping screw	219925
Effective Ø D	37 mm
Overhang L ₁	98 mm
Number of cutting edges Z	1
Number of clamping slots	1
Overall length L	160 mm
Shank type	Weldon shank

Application for type of drilling	Blind hole
Application for type of drilling	Through hole
Cutting direction	left-hand and right-hand
Through-coolant	yes
Type of product	thread milling cutter

Accessories

Clamping screw	219925
----------------	--------