


DCGT 11T301, Grade: PR1725

Order data

Order number	260384 PR1725
GTIN	4960664923434
Item class	25E

Technical description

Secondary application	P
Cutting depth a_p	0.2 - 1.5 mm
Tolerance	G
Cutting speed v_c secondary application	50 - 150 m/min
Feed f	0.03 - 0.2 mm/rev.
Corner radius	0.1 mm
Grade	PR1725
Cutting conditions	slightly interrupted
Coating	coated
Tool material	Carbide
Finishing/roughing assignment	Finishing
Chip breaker	MFP-SKS

ISO code indexable insert	DCGT 11T301
Cutting speed v_c main application	60 - 200 m/min
Main application	M
Number of changes/inserts	2
Type of product	Indexable insert for turning