


**CC.T 060204, Grade: PDL010****Order data**

Order number	260092 PDL010
GTIN	4960664882458
Item class	25E

Description

CC.T 060204 PDL010 Grade: PDL010
Chip breaker: AP
Tolerance: G
Cutting depth a_p : 0.1 - 1 mm
Feed f : 0.05 - 0.25 mm/rev.
Cutting speed v_c main application: 100 - 400 m/min

Technical description

Coating	coated
Cutting speed v_c main application	100 - 400 m/min
Cutting depth a_p	0.1 - 1 mm
Main application	N
ISO code indexable insert	CC.T 060202
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing

Grade	PDL010
Tolerance	G
Feed f	0.05 - 0.25 mm/rev.
Tool material	Carbide
Number of changes/inserts	2
Cutting conditions	slightly interrupted
Chip breaker	AP
Type of product	Indexable insert for turning