



MaxX lifting magnet, maximum loading capacity (level): 200kg



Order data

Order number	382001 200
GTIN	
Item class	38D

Description

Version:

Compact robust design with neodymium permanent magnets. Stray magnetic flux is prevented by the "neutral crown" principle, thus preventing undesirable attraction forces acting on adjacent loads. The base body is made from a single block without any weld seams, thus ensuring constant capability. The lever has a lock which prevents accidental release of the load. Certified break-away force.

Application:

Quick and easy handling and transport of flat and round materials with 3-fold safety.

Technical description

maximum lifting capacity round	100 kg
Dimension F	133 mm
Dimension D	79 mm
Dimension E	63 mm
Dimension C	79 mm
maximum lifting capacity flat	200 kg

maximum length flat	1500 mm
minimum material wall thickness, round	10 mm
Dimension B	160 mm
Dimension A	110 mm
maximum Ø round	300 mm
Weight	4.5 kg
minimum material wall thickness, flat	20 mm
Dimension G	35 mm
Type of product	Lifting magnet