



## MaxX lifting magnet, maximum loading capacity (level): 600kg



### Order data

Order number	382001 600
GTIN	
Item class	38D

### Description

#### Version:

Compact robust design with neodymium permanent magnets. Stray magnetic flux is prevented by the "neutral crown" principle, thus preventing undesirable attraction forces acting on adjacent loads. The base body is made from a single block without any weld seams, thus ensuring constant capability. The lever has a lock which prevents accidental release of the load. Certified break-away force.

#### Application:

Quick and easy handling and transport of flat and round materials with 3-fold safety.

### Technical description

minimum material wall thickness, round	15 mm
Dimension E	88 mm
maximum $\varnothing$ round	400 mm
maximum lifting capacity flat	600 kg
Dimension D	101 mm
maximum length flat	2000 mm

Dimension A	234 mm
minimum material wall thickness, flat	25 mm
Dimension G	52 mm
Dimension B	285 mm
maximum lifting capacity round	250 kg
Dimension F	176 mm
Dimension C	106 mm
Weight	18 kg
Type of product	Lifting magnet