

metabo**Cordless hammer drill with Li-ion battery, Type: SB18LTXBLI****Order data**

Order number	070121 SB18LTXBLI
GTIN	4061792187849
Item class	03D

Description**Version:****Cordless hammer drill with brushless motor and two-speed gearbox.**

Choose between a complete set of 2 battery packs, charger and sturdy plastic case or the machine without accessories in a box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

By the way, all Metabo battery packs come with a 3-year warranty, irrespective of the number of charging cycles.

Further details such as the bright LED work light and the handy belt hook ensure even more comfort when working. All LT and LTX models are equipped with a high-performance impact mechanism for maximum drilling performance in stone and masonry. The pulse operation of the LTX class provides effective help when screws are tight or when spot drilling on smooth surfaces. For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

- **Cordless hammer drill with maximum power for the most demanding applications.**
- **Selectable pulse operation for unscrewing fixed screws and spot drilling on smooth surfaces.**
- **Precision stop: electronic torque coupling with increased precision for precise, sensitive working.**
- **Electronic safety shut-off: no kick-back when blocking the drill – for high user protection.**

- **Integrated LED work light with afterglow function for optimum brightness in the work area.**
- **With practical belt hook and bit depot, optionally fixable on the right or left.**
- **Many brands, one battery system: this product can be combined with all 18V battery packs and chargers of the CAS brands.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

Supplied with:

Supplied with quick-clamping drill chuck, 2× Li-ion batteries, charger and metaBox.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

maximum torque hard	130 Nm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Power supply	Rechargeable battery-powered
maximum torque soft	65 Nm
Packaging	Metabox
Weight including rechargeable battery	2.5 kg
Manufacturer's designation	SB 18 LTX BL I
No load speed	0
No load speed	0 - 2000
Battery capacity	4 Ah
Weight without battery	1.8 kg
maximum twist drill size Ø in wood	68 mm
Motor design	brushless
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in concrete	16 mm
Battery voltage	18 V
Number of rechargeable batteries contained	2
typical application	Heavy Duty

maximum twist drill size Ø in steel	13 mm
Quick-clamping chuck range	1.5 - 13 mm
Type of product	Impact drill /screwdriver