

metabo
Cordless hammer drill without rechargeable battery, Type: KHLTXBL28Q

Order data

Order number	075561 KHLTXBL28Q
GTIN	4061792218604
Item class	03D

Description
Version:
Power packs for hammer drilling.

The hammer drill has a high-performance hammer action with a precise pneumatic impact mechanism that generates impacts with maximum impact energy with minimal pressure.

Metabo Quick: fast, tool-free chuck change.

Combination hammer drill with 3 functions: **hammer drilling, drilling and chiselling.**

- **Metabo VibraTech (MVT): health-friendly, low-fatigue working even in continuous use.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics for working with material-appropriate speeds that remain constant under load.**
- **Safety shut-off: mechanical decoupling of the drive when the drill is blocked for safe working.**
- **Extremely light and handy cordless hammer with integrated suction interface.**
- **Maximum drilling performance, efficiency and service life thanks to brushless technology and high-performance impact mechanism.**
- **Dust-free drilling with compact dust extraction ISA 28 (accessories).**
- **Metabo VibraTech (MVT): health-friendly, low-fatigue working even in continuous use.**
- **Optional reduction of speed and impact energy for working in softer materials.**
- **Electronic soft start for precise spot drilling.**
- **LED work light provides a clear view of the bore area.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Without battery and charger.

With additional handle and depth stop. Including hammer chuck and quick-clamping drill chuck.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

suitable battery - supplier / battery type / voltage	Type CAS 18 V
Number of rechargeable batteries contained	0
maximum hammer rate	4470 min ⁻¹
Manufacturer's designation	KH 18 LTX BL 28 Q
maximum twist drill size Ø in wood	30 mm
Battery voltage	18 V
Tool arbor shape	SDS Plus
Weight without battery	3.4 kg
maximum twist drill size Ø in concrete	28 mm
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in steel	13 mm
Impact energy	3 J
No load speed	0 - 1000 min ⁻¹
Power supply	Mains operated
Type of product	Hammer drill